

EXPAK CLOSING SYSTEMS

There are various options available for closing the Nefab ExPak. Nefab can recommend the best closing system based on how the boxes are used in your supply chain.



ExPak

BY NEFAB

Standard Tongue

Our Standard Tongue is the most commonly used option as it has no loose parts. It works well when the box will not be opened and closed several times throughout the supply chain.

Spring Clip and Detachable Tongue


The Spring Clip and the Detachable Tongue can be used when the packaging needs to be opened several times. These two systems require the same mounting plate and can be used in conjunction or independently. These are fast and efficient closing systems.

Plastic Clip

The Plastic Clip can be used several times and is easy to assemble and remove. The benefit with this closing system is that it does not require the steel mounting plate that the Spring and Detachable Tongue use.



Scan the QR code to learn about our ExPak solutions.




Standard Tongue

Standard tongues are pressed into the plywood by Nefab as part of the box. During box assembly, it locks into the slot and is then bent over.



Detachable Tongue

Detachable tongues are supplied loose, are mounted through a steel catchplate and slot in the profile, and is then bent over.



Spring Clip

Spring clips are supplied loose. They are hooked into the steel slot, then mounted into the catchplate and snapped in place.



Plastic Clip

Plastic clips are supplied loose. They hook into the slot in the steel profile and snap through a hole in the plywood to lock in place.

Contact Nefab for advice on which closing system is the best for your ExPak application. Visit us at nefab.com/northamerica/.

NEFAB YOUR
PACKAGING
SOLUTION.